

CE		IP66	EMERGENCY
E27	230V 50Hz		G23 24V DC
Ta -25°C ÷ +40°C 0°C ÷ +40°C version „EM“ -40°C ÷ +60°C version „tF“		Carton (mm/pcs): 410 x 460 x 170 / 1	

To order:



Protective basket
1-99.8535/1



Protective glass
132.5069



Blinding plug
PG11/M16



Ballast box
BOX 2

Type	Recommended light source [W]	Voltage [V/Hz]	Weight [kg]
511 32 01	Halogen bulb Philips EcoClassic 140	230 / 50	4
	Bulb CLAS 200	230 / 50	4
	Blended lamp HWL 160	230 / 50	4
	*High-pressure mercury discharge lamp HQL 80	230 / 50	4
	*High-pressure mercury discharge lamp HQL 125	230 / 50	4
	Compact fluorescent tube DULUX EL 23	230 / 50	4
511 32 24	Bulb for 24 V DC, 100	24 V DC	4
581 01 01	1 x Compact fluorescent tube DULUX S 9/11	230 / 50	4
581 01 02	2 x compact fluorescent tube DULUX S 9/11	230 / 50	4
511 32 01 EM	Compact fluorescent tube DULUX S 9	230 / 50	5
511 32 01 tF	Halogen bulb Philips EcoClassic 140	230 / 50	4
	Bulb CLAS 200	230 / 50	4
	Blended lamp HWL 160	230 / 50	4

* Light fitting provided with a mercury discharge lamp HQL requires a ballast box type BOX 2.

TURTLE



CE	IP66	
	E27	230V 50Hz
Ta -25°C ÷ +40°C -50°C ÷ +80°C version „Ht“		
Carton (mm/pcs): 400 x 400 x 190 / 1		

Use: Light fitting for the illumination of indoor and outdoor industrial spaces.

Technical description:

The light fitting body and flange are AlSi alloy castings finished with powder paint. The optical cover is made of hardened glass. There are two cable outlets on the light fitting sides. Electrical equipment is installed inside the light fitting. The light fitting is designed as a through light fitting. When the light fitting is used as a terminal light fitting, the free cable outlet is blinded with a plug. The max. cross-section of the connecting conductors is 4 mm².

Installation:

On the ceiling, wall or another solid substrate (structure) ensuring firm connection.

To order:



Protective basket
1-99.8534 / 1




Protective glass
232.5070



Blinding plug PG11/
M16



Ballast box
BOX 2



Type	Recommended light source [W]	Voltage [V/Hz]	Weight [kg]
511 33 02	2 x halogen bulb Philips EcoClassic 105	230 / 50	6
	2 x bulb CLAS 200	230 / 50	6
	1 x blended lamp HWL 160	230 / 50	6
	*1 x high-pressure mercury discharge lamp HQL 80	230 / 50	6
	*1 x high-pressure mercury discharge lamp HQL 125	230 / 50	6
	2 x compact fluorescent tube DULUX EL 23	230 / 50	6
511 33 02 Ht	2 x halogen bulb Philips EcoClassic 70	24 V DC	6
	2 x bulb CLAS 100	230 / 50	6

* Light fitting provided with a mercury discharge lamp HQL requires a ballast box type BOX 2.